



物料名称：VP-350说明书
物料编号：YZ77-1
材质：100g双胶/CMYK
展开尺寸：360x210mm
成型尺寸：72x105mm

说明书正面(英文)

Professional Photographic Equipment

INSTRUCTIONS

VP-350

Telephoto Lens Support Plate

GUANGDONG SIRUI OPTICAL CO.,LTD.

Add: The Third Industrial District, Wuguishan Town, Zhongshan City,
Guangdong, China (Zip Code: 528458)
Tel: 86-760-88597373 Fax: 86-760-88207062
E-mail: info@sirui-photo.com Website: www.sirui.com

1. Know your VP-350

VP-350 QR Telephoto Lens Support Plate

2. Attaching the VP-350

1. Know your VP-350

The VP-350 is specially designed for supporting large telephoto lenses. The VP-350 Telephoto Support Plate is designed to fit on the SIRUI Video head (or other video heads with Manfrotto compatible quick release plates).

2. Attaching the VP-350

Attach the Camera QR Plate onto your camera; then attach the Horizontal Adjustment Rail into the Horizontal Adjustment Clamp.

3. VP-350 Operation

- Loosen the Adjustment Clamp Locking Knob and move the Horizontal Adjustment Rail to its lowest position.
- Place the camera onto the lens and attach the lens onto the Telephoto Lens Support Plate by twisting the 1/4\"/>

3. VP-350 Operation

- Move the Horizontal Adjustment Rail up, until it couples with the bottom of the QR Plate on the camera body. Lock the Quick Release Clamp and the Adjustment Clamp Locking Knob.
- If the 1/4\"/>
- Slide the VP-350 onto the Sirui Video Head and tighten the Clamp Locking Knob.

4. Cautions

- To prevent excessive wear to the camera's tripod socket, you should not frequently attach and remove the Quick Release Plate. It is quite common to leave the QR Plate permanently attached to the camera.
- Please hold your camera while attaching and removing it from the QR Clamp.

Dear SIRUI Customer,

Thank you for your purchase of SIRUI Professional Products! SIRUI warrants that your purchase is free from defects in materials and workmanship under normal use during the Limited Warranty Period. The Warranty begins on the original date of purchase on your sales receipt and is not transferable. If service is required, a copy of the sales receipt must be included with an explanation of the problem.

Product	Warranty Length
TriPods / Monopods / Accessories	6 years
Humidity Control Cabinet (Cabinet)	
Humidity Control Cabinet (Electronics)	3 years

Model: _____ Date: _____

Store: _____ Serial Number: _____

Warranty coverage can differ from region to region.

Please see the contact information below for product registration, information and service for the region the product was purchased in.

SIRUI 6 (six) Year Limited Warranty (3 Year Warranty for Electronic Parts). This warranty shall be limited to repair, adjustment and/or replacement at SIRUI or its authorized distributor option, of defective parts, free of charge (except the cost of transportation to the distributor/service center). Responsibility is limited to the actual cost of the item. Call or Email with questions and service before sending any product to the center in your region. Below is a listing of contact information for Product Registration, Service Inquiries and Questions. SIRUI will not be responsible for expenses or inconveniences, or consequential damages to equipment, or by breach of any experience or implied warranties.

Limitations:

Warranty is not transferable. This warranty covers all defects encountered in normal use of the equipment and does not apply in the following cases:
1. If the equipment has been serviced by other than an authorized SIRUI Service Center.
2. Damage to the equipment is due to modification (including but not limited to, the removal of ballhead clamps), overloading, mishandling, abuse, accident, sand, corrosives, water damage or not following operating instructions.
3. No valid proof of purchase is provided.
4. Damage caused by acts of nature (including, but not limited to fires, floods or earthquakes).

Warranty coverage can differ from region to region. Please see contact information below for product registration, information and service for the region the product was purchased in.

Warranty Address and Contact Information:

(Please contact the seller or the local distributor where the product was purchased for warranty issues or questions and before any product is sent.)

1. Guangdong SIRUI Optical Co., Ltd.
The Third Industrial District, Wuguishan Town, Zhongshan City, Guangdong, China
Tel: 0086-760-88897373 Fax: 0086-760-88207062
Http://www.sirui.com E-mail: info@sirui-photo.com
Service Hotline: 0086-400 830 2299

2. SIRUI USA, LLC
Add: 29 Commerce Court Verona, NJ 07044
www.siriususa.com
Service: Toll Free 866-373-0829 E-mail: info@sirui.com
FOR PRODUCTS PURCHASED IN THE USA PLEASE SEE:
For full details on USA Warranty Terms and Limitations:
https://www.siriususa.com/warranty.html
To register products: https://www.siriususa.com/product-registration.html

3. Focus Nordic AB
For technical support, service or repairs, please contact:
Sweden: info@focusnordic.se www.focusnordic.se
Norway: info@focusnordic.no www.focusnordic.no
Denmark: info@focusnordic.dk www.focusnordic.dk
Finland: info@focusnordic.fi www.focusnordic.fi
Iceland: info@focusnordic.is www.focusnordic.is
Latvia: info@focusnordic.lv www.focusnordic.lv
Estonia: info@focusnordic.ee www.focusnordic.ee
Lithuania: info@focusnordic.lt www.focusnordic.lt
Poland: info@focusnordic.pl www.focusnordic.pl

4. TSE Imaging BV
Add: Argonweg 135, 1362AD Almere, The Netherlands
Telephone: +31 (0)36 8450348 E-mail: service@tse-imaging.nl
(Exclusive Distributor for Netherlands, Belgium, Luxembourg)
www.sirui-photo.nl

5. 대광엔터테인먼트
한국 총판, 기술지원 및 보정서비스 제공.
서울특별시 중구 남대문로 10, 1층
Tel: 02-752-3304 Fax: 02-774-9903
www.sirui.co.kr loweprokr@gmail.com

Specifications are subject to change without notice.

VP-350 420×90×145 236g/76.36g

Weight

Specifications

VP-350 Data Chart

说明书背面(中文)

影像随心 思锐随行

使用说明

VP-350长镜头支撑系统

广东思锐光学股份有限公司

地址: 广东省中山市五桂山第三工业区 邮编: 528458
电话: 0760-88897373 传真: 0760-88207062 服务热线: 400 830 2299
邮箱: info@sirui-photo.com 网址: www.sirui.com

1. 认识VP-350

2. 安装VP-350

1. 认识VP-350

VP-350长镜头支撑系统专为支撑摄影用长焦镜头而设, 建议配合思锐摄像机云台使用。

2. 安装VP-350

- ① 从包装中取出配件, 将水平夹座快装板安装在水平夹座上, 然后将竖向滑动快装板安装到竖向夹座上。
- ② 将准备好的VP-350安装到思锐摄像机云台上, 锁紧云台夹座旋钮。

3. VP-350的基本操作

- ① 先将相机和长镜头安装在一起, 再把水平夹座快装板安装到相机的底部。
- ② 将准备好的长镜头座放置在VP-350的防滑垫板上, 目测相机底部的水平夹座快装板处于水平夹座的上方, 利用VP-350快装板上1/4"和3/8"螺丝对镜头座进行连接固定。
- ③ 滑动竖向滑动快装板, 让水平夹座快装板与水平夹座配合, 然后锁紧。如快装板与夹座没对齐, 可以适当松开长镜头

3.VP-350的基本操作

座螺丝, 调整镜头座在VP-350快装板上的位置, 直到两处都能配合, 这时可以旋紧螺丝以及夹座锁紧旋钮, 锁紧设备。

- ④ 如水平夹座快装板上的1/4"螺丝与相机底部螺孔不匹配, 可以将1/4"螺丝拧下, 水平夹座快装板可以直接作为支撑相机之用。

4. 注意事项

- ① 建议不要经常从设备上拆装快装板, 以避免损坏设备的安装螺丝孔。
- ② 在安装摄影设备时, 请用手扶稳设备, 以防意外跌落。

保修卡

尊敬的顾客:

感谢您购买思锐的产品! 在正常使用过程中, 如果因器材本身的材料工艺出现质量问题, 思锐将会提供免费维修服务。在需要保修服务时, 须提供本保修卡和购买凭证(收据或发票, 须有商家盖章)。思锐公司售后服务热线: 400 830 2299

产品名称	保修期限
脚架	6年
云台	
防潮柜本体	
电子部分	3年

产品型号: _____ 购买日期: _____

商店名称: _____ 商店电话: _____

商店地址: _____

商店盖章: _____

顾客须知:

- (1) 思锐产品, 享5年免费保修(电子部分为3年), 保修时间从购买之日起算。
- (2) 所有保修产品, 必须是在思锐正式授权的经销商或电子商务站所购买。
- (3) 寄件时请附上“维修单”, 请先拨打思锐服务电话, 待确认故障后, 思锐公司将派员上门维修, 一般性故障可在5个工作日内完成维修并寄回。
- (4) 所需维修的配件, 请先确定发生故障的部件, 把故障件卸下并带回思锐工厂检测即可, 其余可继续使用或延长或致电服务热线。
- (5) 以下情况不在保修范围:
 - ① 超过保修期限的;
 - ② 在未获正式授权经销商处购买的;
 - ③ 在未获正式授权和代售商私自拆机中心维修过的;
 - ④ 由于不正当操作、意外事件、自然灾害导致的故障或损坏。

※ 本保修卡只限在中国大陆使用

维修登记表A

用户姓名	
用户电话	
用户地址	
部 门	
故障维修描述	
维修人员签名	
维修时间	

维修登记表B

用户姓名	
用户电话	
用户地址	
部 门	
故障维修描述	
维修人员签名	
维修时间	

思锐公司保留产品升级和由于产品升级而变更参数的权利, 请以实物为准, 恕不另行通知。
印刷品上如有印刷错误或遗漏方面的错漏如造成不便, 敬请包涵。



VP-350 长镜头

VP-350 420×90×145 670


重量

规格


说明书折叠方法:



宽度72MM为一折,依次循环,
直到折完为止,共5折



成品形状



成品尺寸

包装工程师：彭少章

审核：

翻译:

批准: