


物料名称：LE-60说明书  
物料编号：YCM32-1  
材质：100g双胶/CMYK  
展开尺寸：285x210mm  
成型尺寸：72x105mm


说明书正面(英文)



Professional Photographic Equipment

# INSTRUCTIONS

## LE-60 Leveling Base



GUANGDONG SIRUI OPTICAL CO., LTD.  
Add: The Third Industrial District, Wugushan Town, Zhongshan City, Guangdong, China (Zip Code: 528458)  
Tel: 86-760-88897373 Fax: 86-760-88207062  
E-mail: info@sirui-photo.com Website: www.sirui.com

### 1. Know your leveling base




Fig 1

### 2. Attaching your leveling base




Fig 2-1 Fig 2-2

### 3. Using the Leveling base




Fig 3

### 1. Know your leveling base

### 2. Attaching your leveling base






① Attach the Leveling base onto the tripod as shown in Fig. 2-1, align the 3/8" screw hole of the base with the 3/8" mounting screw of the tripod.

② If you want to directly attach a camera to the Leveling Base, remove the 3/8" adapter nut from the 1/4" Mounting Screw. If you want to connect a ball head onto the Leveling Base, make sure the 3/8" adapter nut is on the 1/4" Mounting Screw and attach as shown in Fig. 2-2.

### 3. Using the Leveling base

① To prevent a ball head from unscrewing from the Leveling Base, use an Allen key to adjust the Ball Head Locking Screw so that it presses against the base of the Ball Head. Do not use excessive force. Use all 3 Ball Head Locking Screws for best results. Remember to loosen the Ball Head Locking Screw before removing the ball head.

② As shown in Fig. 3, loosen the Leveling Control Locking Knob and adjust the Leveling Ball to the desired angle (use the bubble level on the platform for precise alignment), tighten the Leveling Control Locking Knob.

LE-60	60/2.4	44/1.7	0.29/0.64	30/66.1
kg/lb	mm/inch	mm/inch	kg/lb	kg/lb
				
Maximum Load	Maximum Height	Maximum Width	Maximum Weight	Maximum Diameter

LE-60 Data Chart

### WARRANTY CARD/INFORMATION

Dear SIRUI Customer,  
Thank you for your purchase of SIRUI Professional Products!  
SIRUI warrants that your purchase is free from defects in materials and workmanship under normal use during the Limited Warranty Period. The Warranty begins on the original date of purchase on your sales receipt and is not transferable. If service is required, a copy of the sales receipt must be included with an explanation of the problem.

Product	Warranty Length
Tripods / Monopods / Accessories	6 years
Humidity Control Cabinet (Cabinet)	3 years
Humidity Control Cabinet (Electronics)	3 years

Model: \_\_\_\_\_ Date: \_\_\_\_\_  
Store: \_\_\_\_\_ Serial Number: \_\_\_\_\_

**Warranty coverage can differ from region to region. Please see the contact information below for product registration, information and service for the region the product was purchased in.**  
SIRUI 6 (six) Year Limited Warranty (3 Year Warranty for Electronic Parts). This warranty shall be limited to repair, adjustment and/or replacement at SIRUI or its authorized distributors option, of defective parts, free of charge (except the cost of transportation to the distributor/service center). Responsibility is limited to the actual cost of the item. Call or Email with questions and service before sending any product to the center in your region. Below is a listing of contact information for Product Registration, Service Inquiries and Questions. SIRUI will not be responsible for expenses or inconveniences, or consequential damages to equipment, or by breach of any expressed or implied warranties.

**Limitations:**  
Warranty is not transferable.  
This warranty covers all defects encountered in normal use of the equipment and does not apply in the following cases:  
1. If the equipment has been serviced by other than an authorized SIRUI Service Center.  
2. Damage to the equipment is due to modification (including but not limited to, the removal of ballhead clamps), overloading, mishandling, abuse, accident, sand", corrosives, water damage" or not following operating instructions.  
3. No valid proof of purchase is provided.  
4. Damage caused by acts of nature (including, but not limited to fires, floods or earthquakes).

Warranty coverage can differ from region to region. Please see contact information below for product registration, information and service for the region the product was purchased in.


**Warranty Address and Contact Information:**  
(Please contact the seller or the local distributor where the product was purchased for warranty issues or questions and before any product is sent.)

1. Guangdong SIRUI Optical Co., Ltd.  
The Third Industrial District, Wugushan Town, Zhongshan City, Guangdong, China  
Tel: 0086-760-88897373 Fax: 0086-760-88207062  
Http://www.sirui.com E-mail: info@sirui-photo.com  
Service Hotline: 0086-400 830 2299  
Complaint Hotline: +86-181 6563 9388  
(Monday to Friday: 8:15am-12:15pm, 14:00pm-18:00pm)

2. SIRUI USA, LLC  
Add: 29 Commerce Court Verona, NJ 07044  
www.sirui.com  
Service: Toll Free 866-373-0829 E-mail: info@sirui.com  
FOR PRODUCTS PURCHASED IN THE USA PLEASE SEE:  
For full details on USA Warranty Terms and Limitations:  
https://www.siruiusa.com/warranty.html  
To register products: https://www.siruiusa.com/product-registration.html

3. European Service Center  
Add: SIRUI Optical GmbH • Ernst-Augustin-Str. 1a • 12489 Berlin • Germany  
Phone: +49 30 991 94 94 00 • Email: info@siruioptical.eu


说明书背面(中文)



影像随心 思锐随行

# 使用说明

## LE-60水平调节台



广东思锐光学股份有限公司  
地址：广东省中山市五桂山第三工业区 邮编：528458  
电话：0760-88897373 传真：0760-88207062 服务热线：400 830 2299  
邮箱：info@sirui-photo.com 网址：www.sirui.com  
投诉电话：18165639388  
(上班时间: 9:15-12:15, 14:00-18:00)

### 1.认识水平调节台




图1

### 2.安装水平调节台




图2-1 图2-2

### 3.基本操作




图3

### 1.认识水平调节台（图1所示）

### 2.安装水平调节台






① 按图2-1所示将水平调节台安装于三脚架上，把底座上的3/8"螺丝孔对准脚架上的3/8"转接螺丝，然后顺时针旋转底座至牢固为止。

② 如果你想直接把相机安装到水平调节台上，把3/8"连接螺帽从1/4"转接螺丝上拧下。如果你想连接一个云台到水平调节台上，确保3/8"连接螺帽如图2-2所示，安装在1/4"转接螺丝上。

### 3.基本操作

① 为防止连接云台和水平调节台的螺钉松动，用六角板手调节云台紧定螺钉，以使螺钉紧连着云台的底部，用力不要过大。使用3个云台紧定螺钉会使效果更好。在拆除云台之前，请记得要先松开云台紧定螺钉。

② 如图3所示，松开水平控制锁紧旋钮，调节半球体达到所需要的角度（用水平调节台上的水平珠来实现精准校对），然后锁紧水平控制锁紧旋钮。

LE-60	60	44	0.29	30
mm	mm	mm	kg	kg
				
最大负载	最大高度	最大宽度	最大重量	最大直径

09-31

### 保修卡

尊敬的顾客：  
感谢您购买思锐的产品！在正常使用过程中，如果因器材本身的材料及工艺出现质量问题，思锐将为您提供免费的保修服务。在需要保修服务时，请提供本保修卡和购买凭证（收据或发票，须有商家盖章）。  
思锐公司售后服务热线：400 830 2299

产品名称	保修期限
脚架	6年
云台	
防潮柜本体	
电子部分	3年

产品型号：\_\_\_\_\_ 购买日期：\_\_\_\_\_  
商店名称：\_\_\_\_\_ 商店电话：\_\_\_\_\_  
商店地址：\_\_\_\_\_  
商店盖章：\_\_\_\_\_  
顾客须知：  
① 思锐产品，享受6年免费保修（电子部分为3年），保修时间从购买之日起算起。  
② 质保产品，必须是在思锐正式授权的经销商或电子商务处购买。  
③ 寄件时请附上“维修单”，请先拨打思锐服务电话，经确认后，思锐公司将免费上门，一般性故障将在2个工作日内完成维修并取件。  
④ 故障维修的保修，请先确定发生问题的部件，把故障部件单独寄到思锐工厂维修即可。具体可参照使用说明书或致电服务热线。  
⑤ 以下情况不在保修范围：  
① 超过保修期限的；  
② 在非思锐正式授权经销商处购买的；  
③ 在未报思锐授权的代理商或维修中心维修过的；  
④ 由于不正当操作、意外事件、自然灾害等导致的故障或损伤。

※ 本保修卡只限在中国大陆使用

### 维修登记表A

用户姓名	
用户电话	
用户地址	
邮编	
故障维修描述	
维修人员签名	
维修时间	

### 维修登记表B

用户姓名	
用户电话	
用户地址	
邮编	
故障维修描述	
维修人员签名	
维修时间	

说明书折叠方法:

